


MEDI LED

A range of low profile surface mounted IP40 LED luminaires.

- Extruded polycarbonate diffuser with an LED specific opal lining.
- Offers superior efficiency and lifetime to equivalent fluorescent versions.
- Polycarbonate moulded white end caps.
- Colour temperature – available in 3000K and 4000K versions.
- Colour rendering index Ra >80.
- Predicted lifetime >50,000 hours.
- No ultra violet or infra red emissions.
- Available in fixed output DALI/DSI or Switchdim operation.
- Standard, self test and DALI reporting 3 hour maintained emergency conversions are available.
- Available with separate built in nightlight.
- Available with end cap mounted miniature PIR with switched or dimmed photocell.
- Photometric data available in Eulumdat format on request or via Relux website.
- Standard ITAB Prolight LED warranty (see page 161).



Wattage	A (mm)	B (mm)
28/35W	1175	870
35/49W	1483	1170



Catalogue No.	Nom Dimensions (mm)	LED Flux (Lumens)	Luminaire Flux (Lumens)	LED Wattage	Total System Wattage	Luminaire Lumens / Circuit Watt	Colour Temp	CRI	Weight (Kg)
MEDI/122/F/52/4K	1200	5200	3354	30.0	33.0	101.6	4000K	>80	3.5
MEDI/122/F/59/4K	1200	5920	3818	35.1	38.6	98.9	4000K	>80	3.5
MEDI/152/F/65/4K	1500	6500	4193	37.5	41.3	101.6	4000K	>80	4.3
MEDI/152/F/74/4K	1500	7400	4773	43.8	48.2	99.1	4000K	>80	4.3

Colour Temperature: To specify 3000K colour temperature replace '3K' in catalogue number: e.g. MEDI/152/F/65/3K

Dimmable Drivers: To specify DALI driver replace 'F' in catalogue number with 'X': e.g. MEDI/122/X/59/4K

To specify DALI driver wired for Switchdim operation replace 'F' in catalogue number with 'S': e.g. MEDI/152/S/65/4K

Emergency Conversion: To specify 3 hour maintained emergency packs, add 'E' to catalogue number: e.g. MEDI/122/F/59E/4K

Self Test Emergency Conversion: To specify 3 hour maintained self test emergency packs, add 'ES' to catalogue number: e.g. MEDI/152/F/74ES/4K

Nightlight: An LED nightlight can be supplied. 470 lumens, colour 3500K, 4.5W. Add suffix 'N' to catalogue number: e.g. MEDI/122/F/59N/4K

PIR/Photocell: To add an end mounted PIR/Photocell add suffix 'PC' to catalogue number: e.g. MEDI/122/F/59/4K/PC